

## Machine equipment / Fish skinning machines

machine model	automatic machine with infeed and output conveyor	open top stand machine	open top table machine	underframe	skinning technology	skinning modes			blade holder spring suspended	NOCK ACTIVE SKIN GRIPPER®	NOCK POWER PLATES®	NOCK EASY-FLOW® safety cover	lockable castors	stainless steel
						silver skinning	thin (shallow) skinning	deep skinning						
Freeze Drum Skinner TFE 350	<input checked="" type="checkbox"/>				GF		<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	rotating band knife		<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Cortex CBF 496	<input checked="" type="checkbox"/>				CF	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Cortex CBF 496 SALMON	<input checked="" type="checkbox"/>				CF	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Skinex SB 496	<input checked="" type="checkbox"/>				S	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Skinex QS 888	<input checked="" type="checkbox"/>				S	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Cortex CF 460		<input checked="" type="checkbox"/>			CF	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>			<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Skinex S 460		<input checked="" type="checkbox"/>			S	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>				<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Cortex CF 420			<input checked="" type="checkbox"/>	<input type="checkbox"/>	CF	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>					<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Skinex S 420			<input checked="" type="checkbox"/>	<input type="checkbox"/>	S	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>					<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>
Cortex CF 300 COUNTERBOY			<input checked="" type="checkbox"/>	<input type="checkbox"/>	CF	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>					<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>

### Other options (depending on machine model):

- inflated pressure balloon (soft balloon)
- discharge conveyor for removed skin
- transport roller with coarse or fine toothing
- foot switch for „manual“ operation with an open conveyor machine
- turn-around device to skin both sides of flat fish

**standard**

**optional**

**1** restricted

**2** freeze drum hard-anodized

CF = tooth roller with scraper comb

GF = freeze drum

S = transport roller without grooves, with counter rotating cleaning roller